
































ALC25250501-0502电柜 (第六十批)




序号	内部号	型式	简图	数量	颜色	检测内容	备注
1	4332	I48750D04 D14		1		①确认颜色正确 ②确认无毛刺	☒ ☒
2	4746	5517532		1		确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
3	4747	5517533	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒
4	4751	5517538	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒
5	4748	5517535	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒
6	4749	5517536	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒
7	4750	5517537	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒
8	4752	5517539	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒
9	4753	5517540	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒
10	4754	5517541	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒
11	4755	5517542	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒

12	4756	5517544	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒	
13	4757	5537196	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒	
14	4758	5537197	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒	
15	4759	5517545	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒	
16	4760	5517546	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒	
17	4761	5517547	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒	
18	4762	5517548	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☒	
19	4333	5517549		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
20	4334	5517550		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
21	4335	5517551		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
22	4336	5517955		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	

23	4337	H2B053A02C		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	
24	4338	5517553		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
25	4341	H2601611A01		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
26	4343	5517555		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
27	4344	5517556		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
28	4347	5517559		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
29	4348	5517561		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
30	4349	5517562		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
31	4350	5517563		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
32	4351	5517564		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
33	4353	5517565		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	

34	4354	5517566		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
35	4355	5517567		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
36	4356	5517568		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
37	4357	5517569		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	左右各1件
38	4358	5517570		2	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
39	4359	H2B050A02		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	
40	4360	5517552		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
41	4361	5517560		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
42	4364	H2A901A01		2	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	NBR
43	4367	R2W1013-S01		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
44	4763	5548006		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	

45	4764	X10334A02		3	R海绵 T	①确认颜色正确 ②确认无毛刺	☒ ☒	
46	4765	H2601609A01		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
47	4766	X10262A02		2	R海绵 T	①确认颜色正确 ②确认无毛刺	☒ ☒	
48	4767	5548892		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
49	4768	5548895		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
50	4772	5548884		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
51	4772	5548884		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
52	4773	5549869		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
53	4774	5549870		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
54	4971	H1405660B02		1	黑平	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
55	5322	19X0007-09-S01		1	电镀	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	

56	5323	19X0007-09-S02		1	电镀	①确认颜色正确 ②确认无毛刺	☒ ☒
57	5415	5517579		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒
58	5416	5517580		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
59	5417	5518903		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
60	5418	5587996		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒