

































ALC25251103-1104电柜2台 (27批)


序号	内部号	型式	简图	数量	颜色	检测内容	备注
1	#N/A	I48750D04 D14		1		①确认颜色正确 ②确认无毛刺	☒ ☒
2	4333	5517549		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
3	4334	5517550		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
4	4335	5517551		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
5	4336	5517955		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
6	4337	H2B053A02C		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒
7	4338	5517553		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
8	4341	H2601611A01		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
9	4343	5517555		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
10	4344	5517556		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
11	4347	5517559		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒

12	4348	5517561		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☐ ☒ ☒ ☒	
13	4349	5517562		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
14	4350	5517563		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☐ ☒ ☒ ☒	
15	4351	5517564		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
16	4353	5517565		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
17	4354	5517566		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☐ ☒ ☒ ☒	
18	4355	5517567		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
19	4356	5517568		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☐ ☒ ☒ ☒	
20	4357	5517569		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☐ ☒ ☐ ☒	左右各1件
21	4358	5517570		2	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
22	4359	H2B050A02		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	

23	4360	5517552		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☐	
56	4361	5517560		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☐ ☒ ☒ ☐	
24	4364	H2A901A01		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☐ ☒ ☒ ☒	NBR
25	4746	5517532		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☐	
26	4747	5517533	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☐ ☒	
27	4748	5517535	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☐ ☒	
28	4749	5517536	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☐ ☒	
29	4750	5517537	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☐ ☒	
30	4751	5517538	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☐ ☒	
31	4752	5517539	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☐ ☒	
32	4753	5517540	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☐ ☒	

33	4754	5517541	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
34	4755	5517542	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
35	4756	5517544	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
36	4757	5537196	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
37	4758	5537197	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
38	4759	5517545	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
39	4760	5517546	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
40	4761	5517547	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
41	4762	5517548	焊在柜上	1		①确认颜色正确 ②确认无毛刺	☒ ☐
42	4763	5548006		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
43	4764	X10334A02		1	R海绵T	①确认颜色正确 ②确认无毛刺	☒ ☐

44	4765	H2601609A01		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
45	4766	X10262A02		3	R海绵 T	①确认颜色正确 ②确认无毛刺	☒ ☐
46	4767	5548892		3	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
47	4768	5548895		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
48	4769	5517581		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☐
49	4770	5517582		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
50	4771	5518904		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
51	4772	5548884		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
52	4773	5549869		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
53	4774	5549870		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☐
54	4971	H1405660B02		1	黑平	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☐ ☐ ☐

55	5933	B6803150A02		1	黑平	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
----	------	-------------	--	---	----	----------------------------------	--