





































ALC25251201-1202电柜 (35)

序号	内部号	型式	简图	数量	颜色	检测内容	备注
16	4333	5517549		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
17	4334	5517550		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
18	4335	5517551		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
37	4336	5517955		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
20	4338	5517553		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
49	4341	H2601611A01		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
21	4343	5517555		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
22	4344	5517556		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
23	4347	5517559		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
25	4348	5517561		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
26	4349	5517562		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒

27	4350	5517563		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
28	4351	5517564		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
29	4353	5517565		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
30	4354	5517566		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
31	4355	5517567		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
32	4356	5517568		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
33	4357	5517569		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	左右各11
34	4358	5517570		2	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
51	4359	H2B050A02		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	
19	4360	5517552		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
24	4361	5517560		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	

50	4364	H2A901A01		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	NBR
1	4746	5517532		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
2	4747	5517533	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
3	4748	5517535	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
4	4749	5517536	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
5	4750	5517537	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
6	4751	5517538	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
7	4752	5517539	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
8	4753	5517540	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
9	4754	5517541	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
10	4755	5517542	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	

11	4756	5517544	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
39	4757	5537196	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
40	4758	5537197	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
12	4759	5517545	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
13	4760	5517546	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
14	4761	5517547	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
15	4762	5517548	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
41	4763	5548006		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
54	4764	X10334A02		3	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
48	4765	H2601609A01		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
53	4766	X10262A02		3	0	①确认颜色正确 ②确认无毛刺	☒ ☒	

43	4767	5548892		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
44	4768	5548895		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
35	4769	5517581		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	
36	4770	5517582		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
38	4771	5518904		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
42	4772	5548884		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
45	4773	5549869		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
46	4774	5549870		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
47	4971	H1405660B02		1	黑平	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☐	
52	5876	H2B053A02		1	光泽镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	