































ALC25251203电柜 (35)

序号	内部号	型式	简图	数量	颜色	检测内容	备注
1	4333	5517549		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
2	4334	5517550		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
3	4335	5517551		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
4	4336	5517955		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
5	4338	5517553		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
6	4341	H2601611A01		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
7	4343	5517555		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
8	4344	5517556		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒
9	4347	5517559		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
10	4348	5517561		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒
11	4349	5517562		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒

12	4350	5517563		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
13	4351	5517564		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
14	4353	5517565		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☐	
15	4354	5517566		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
16	4355	5517567		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
17	4356	5517568		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
18	4357	5517569		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	左右各11
19	4358	5517570		2	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
20	4359	H2B050A02		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	
21	4360	5517552		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
22	4361	5517560		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	

23	4364	H2A901A01		1	三价镀锌	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	NBR
24	4746	5517532		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
25	4747	5517533	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
26	4748	5517535	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
27	4749	5517536	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
28	4750	5517537	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
29	4751	5517538	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
30	4752	5517539	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
31	4753	5517540	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
32	4754	5517541	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
33	4755	5517542	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	

34	4756	5517544	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
35	4757	5537196	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
36	4758	5537197	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
37	4759	5517545	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
38	4760	5517546	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
39	4761	5517547	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
40	4762	5517548	焊在柜上	1	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
41	4763	5548006		2	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
42	4764	X10334A02		3	0	①确认颜色正确 ②确认无毛刺	☒ ☒	
43	4765	H2601609A01		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
44	4766	X10262A02		3	0	①确认颜色正确 ②确认无毛刺	☒ ☒	

45	4767	5548892		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
46	4768	5548895		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
47	4769	5517581		1	三价镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	
48	4770	5517582		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
49	4771	5518904		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
50	4772	5548884		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
51	4773	5549869		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
52	4774	5549870		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	
53	4365	H1405998A01		1	黑平	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	
54	5876	H2B053A02		1	光泽镀锌	①确认颜色正确 ②确认无毛刺	☒ ☒	