























ALC25251102(33批) 本体

序号	T号	型式	简图	数量	颜色	检测内容	备注
1	1	5413214		1	白平	①确认颜色正确 ②确认无毛刺	☒ ☒ B
2	1	5413820		1	灰平	①确认颜色正确 ②确认无毛刺	☒ ☒ B
3	1	H0004079A01		1	黑平	①确认颜色正确 ②确认无毛刺	☒ ☒ B
4	1	H0104296B01		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒ B
5	1	H0104343A01		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒ B
6	1	H0504731B02		1	白平	①确认颜色正确 ②确认无毛刺	☒ ☒ B
7	1	H0504732A02		1	黑平	①确认颜色正确 ②确认无毛刺	☒ ☒ B
8	1	H0504920A03		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒ A
9	1	H1406021A01		1	白平	①确认颜色正确 ②确认无毛刺	☒ ☒ A
10	1	H1502976B01		1	白平	①确认颜色正确 ②确认无毛刺	☒ ☒ B
11	1	H1503061A01		1	黑平	①确认颜色正确 ②确认无毛刺	☒ ☒ B

12	1	H1604995A04		1	灰皱	①确认颜色正确 ②确认无毛刺	☒ ☒	B
13	1	H1605084A01		1	黑平	①确认颜色正确 ②确认无毛刺	☒ ☒	B
14	1	H1605378B01		1	白平	①确认颜色正确 ②确认无毛刺	☒ ☒	A
15	1	H1605384A01		1	白平	①确认颜色正确 ②确认无毛刺	☒ ☒	A
16	1	H1605388B02		1	白平	①确认颜色正确 ②确认无毛刺	☒ ☒	B
17	1	H1605682A01		1	白平	①确认颜色正确 ②确认无毛刺	☒ ☒	B
18	1	H3001586A01		1	黑平	①确认颜色正确 ②确认无毛刺	☒ ☒	B
19	1	H3201831A01		1	黑平	①确认颜色正确 ②确认无毛刺	☒ ☒	B
20	1	H0202302B01		1	灰平	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	B
21	1	H0202303A01		1	灰平	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	B
22	1	5504519		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	装配

23	1	5525795		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	B
24	1	5577901		1	灰皱	确认颜色正确 确认无毛刺 确认无变形 过丝确认	☒ ☒ ☒ ☒	A